


SloanLED Layout Estimator User Guide



Logging in to the SloanLED Layout Estimator

Enter your contact details to log in to the SloanLED Layout Estimator. If you request a layout email, it will be sent to your registered email address.

SloanLED®
Leaders in LED Technology

Company:

Name:

Email Address:

State:

Country:

Channel Letter Mode

Channel Letter Mode is the default, but if you switch to Sign Cabinet/Box Mode, you can quickly return to Channel Letter Mode by clicking on the Channel Letter icon. Channel Letter Mode is for single-faced signs only.

Channel Letter Mode **Cabinet Mode** **Height** (Inches or millimeters) **Font** **Stroke** **Depth** (Inches or millimeters) **Product** **Power Supply & Mode** **Language Options** **System of Measurement**


Populate and Save
If you make a change to your layout, click "Populate" to see the result, and then click "Save".

Create PDF

Email PDF File or Request a Quote
Email your finished layout to your registered email address.

24.83" 7 3 7 8 6 5 7 10

SloanLED Layout Estimator User Guide



Editing Channel Letter Layouts


Select a module and use the editing options to improve the final appearance of your layout.

Select Previous Letter **Select Next Letter** **Save** **Undo** **Redo** **Add Module** **Increase Density**

The screenshot shows the SloanLED Layout Estimator software interface. At the top, there are input fields for company name, contact information, and location. Below that is a toolbar with various editing tools. The main workspace displays a channel letter layout for the word 'SloanLED' with dimensions and module counts for each letter. The toolbar includes icons for navigation, editing, and simulation. The layout shows the word 'SloanLED' with dimensions: 'S' is 24.83" high, 'l' is 7" wide, 'o' is 3" wide, 'a' is 7" wide, 'n' is 8" wide, 'L' is 6" wide, 'E' is 5" wide, and 'D' is 7" wide. The total width is 10".

Re-space **Decrease Density** **Rotate Clockwise** **Rotate Counter-clockwise** **Break run** **Connect run** **Add Module at Both Ends** **Flip Module** **Delete Module** **Zoom to Width** **Zoom to Height**

SloanLED Layout Estimator User Guide



Sign Cabinet/Box Mode

For single-sided SignBOX II layouts: The lowest number of rows is optimal for SignBOX II layout designs. Use the height/width that is smallest to determine the direction of the product.

For double-sided SignBOX II layouts: Layout the SignBOX II product vertically for heights of 42" (1067 mm) or higher, as a vertical layout is easier to install. Layout the SignBOX II product horizontally when the height is less than 42" (1067 mm).

Channel Letter Mode

Sign Cabinet/Box Mode

Height (inches or millimeters)

Width (inches or millimeters)

Depth (inches or millimeters)

Language Options

System of Measurement

Populate
If you make a change to your layout, click "Populate" to see the result.

Create PDF

Email PDF File
Email your finished layout to your registered email address.

Product
The SloanLED Layout Estimator will only list the products applicable for the depth and height of your sign.

The screenshot shows a web browser window with the SloanLED website. The interface includes a header with the SloanLED logo and navigation links. Below the header, there are input fields for user information (name, email, location, country). The main content area has a form with fields for Text, Box, Height, Width, Depth, Module, and Power Supply. There are also buttons for Vertical, Horizontal, Double-sided, Populate, PDF, Email PDF File, and Request Quote. A diagram below the form shows a grid of LED modules with dimensions: 96.00" width and 40.00" height. The grid is divided into three rows, each 7.6" high.

SloanLED Headquarters
805.676.3200 • info@SloanLED.com

SloanLED Europe b.v.
+31 88 12 44 900 • Europe@SloanLED.com



SloanLED.com

© 2018 SloanLED Rev A 2018-03-29

